



ARC and TASC Series Features:

- Large, backlit LCD display shows speed, application rate, total applied, working width, distance covered, field area and total area.
- Scan feature monitors and displays all functions.
- Error message system signals misapplication and identifies problem source.
- Ground Speed Override function can be set to match operating conditions.
- All TASC and ARC consoles carry CE certification.
- Non-volatile memory retains settings and data when disconnected from power.
- English and metric operating modes.
- Variable Rate-ready consoles can be connected to Mid-Tech® printers or Mid-Tech Data Link for variable-rate applications.
- Upgradable firmware.



TASC 6500



Data Link

MODEL	NUMBER OF PRODUCTS	LIQUID/DRY	VARIABLE RATE READY	INJECTION READY
ARC 6000	1	Both	No	No
TASC 6100	1	Both	Yes	No
TASC 6200	2	Both	Yes	No
TASC 6300	Carrier + 3 Injection	Liquid	Yes	Yes
TASC 6500	Dual-product + 3 Injection	Both	Yes	Yes
TASC 6600	Carrier + 6 Injection	Liquid	Yes	Yes

PART NUMBER	DESCRIPTION	NOTE	POWER
-------------	-------------	------	-------

CONSOLE KITS (CE VERSION)

PART NUMBER	DESCRIPTION	NOTE	POWER
90-02154	ARC 6000 Console Kit, liquid and dry programming	a	*
90-02160	TASC 6000 Console Kit	a	*
90-02157	TASC 6300 Console Kit	a	*
90-02158	TASC 6600 Console Kit	a	*
90-02155	TASC 6500 Console Kit	a	*
90-02159	TASC 6200 Console Kit	a	*
90-02156	TASC 6100 Console Kit	a	*

OPTIONS

PART NUMBER	DESCRIPTION	NOTE	POWER
401-0010	Console Power Cable, 18'		
401-0102	Console Power Cable Extension, 20'		
45-05013	Console Power Cable, 35'		
815-0009	ARC/TASC Console Mounting Bracket		
851-0010	Console Mounting Knob		

Data Link Module

Data Link modules enable serial communication from all TASC consoles.

- Use a Data Link to connect a TASC console to an external GPS-connected mapping processor to conduct variable rate applications.
- Connects to external device with standard DB-9 serial connector.
- Built-in LEDs confirm communication status.
- Data Link receives power from the console to which it is connected.
- ARC consoles are not compatible with external communications.

How to Order Data Link

PART NUMBER	DESCRIPTION
405-0069-96V	Data Link Module (original protocol)
78-05007	Data Link Module, TASC with 5.0 Software ('98 protocol)

a—Includes an 18' console power cable, mounting knobs, manual and mounting bracket.

*Requires a power lead.