

Nozzle	PSI	110°XR/XRC	TT	TTJ60	AIXR	A13070	A1TTJ60	110°AI/AIC	TTI60	TTI	GPM	GPA $\nabla$ 20" $\nabla$											
		15-60 PSI	15-90 PSI	20-90 PSI	15-90 PSI	20-90 PSI	20-90 PSI	30-115 PSI	20-100 PSI	15-100 PSI		4 mph	5 mph	6 mph	7 mph	8 mph	9 mph	10 mph	12 mph	14 mph	16 mph	18 mph	20 mph
		015	F	VC	—	VC	XC	—	—	—		UC	UC	0.11	8.2	6.5	5.4	4.7	4.1	3.6	3.3	2.7	2.3

Legend for droplet sizes:

- EXTREMELY FINE (XF)
- VERY FINE (VF)
- FINE (F)
- MEDIUM (M)
- COARSE (C)
- VERY COARSE (VC)
- EXTREMELY COARSE (XC)
- ULTRA COARSE (UC)

Diagram illustrating Tip Spacing and GPA Conversion Factor:

- Tip Spacing: 15", 30"
- GPA Conversion Factor: 1.33 (for 15"), 0.67 (for 30")